



DQ302-01
COAT RACK


Included components:



COAT RACK – 1x



CLAMP – 2x



1/4-20 x 3/4"
SBHCS
– 2x



5/8" O.D.
WASHER
– 2x

Tools required for assembly

- Safety glasses
- 5/32" hex key

INSTALLATION: Coat rack only mounts to horizontal slat wall panel.
1. Install coat rack using provided clamp, screw and washer, see Fig. 1.




Fig. 1 – INSTALL COAT RACK

ASSEMBLE WITH CARE! Pangard II® Polyester Powdercoat is a strong, long-lasting finish. To protect this finish during assembly, place unwrapped powdercoated parts on packaging foam or other non-marring surface. Do not place or slide powdercoated parts on concrete or other hard or textured surface – this will damage the finish causing rust to occur. Use touch-up paint on any gouges in the finish caused by assembly tools.